

UP25-H


25 mm Ø, 3 mW - 350 W



KEY FEATURES

- > **MODULAR CONCEPT**
Increase the power capability of your detector:
4 different cooling modules
- > **HIGH PERFORMANCE**
Fast rise time (1.3 s)
High damage threshold (45 kW/cm²)
- > **ENERGY MODE**
Measure single shot energy up to 40 J

OUTPUT OPTIONS

- > **SMART DB15 CONNECTOR**
Contains all the calibration data
- > **integra ALL-IN-ONE-METER**
Connects directly to a PC
Two models available:
 - USB output (-INT)
 - RS-232 output (-IDR)
- > **OPTION SANS-FIL BLU** 
Se connecte via Bluetooth® à un smartphone, une tablette ou un PC

COMPATIBLE DISPLAYS & PC INTERFACES



MIRO ALTITUDE



MAESTRO



TUNER



UNO



U-LINK and P-LINK



S-LINK and M-LINK

ACCESSORIES



Stand with steel post



Extension cables
(4, 15, 20 or 25 m)



Fiber adaptors and connectors
(FC, SC or SMA)



12V power supply







Pelican carrying case

UP25-H

Specifications



	UP25N-40S-H9-D0	UP25N-100H-H9-D0	UP25N-250F-H12-D0	UP25M-350W-H12-D0
MAX AVERAGE POWER (CONTINUOUS / 1 MINUTE)	40 W / 80 W	100 W / 200 W	250 W / 300 W	350 W ^f / 350 W ^f
EFFECTIVE APERTURE	25 mm \emptyset	25 mm \emptyset	25 mm \emptyset	25 mm \emptyset
COOLING METHOD	Convection	Heatsink	Fan-cooled	Water-cooled
MEASUREMENT CAPABILITY				
Spectral range	0.19 - 20 μm	0.19 - 20 μm	0.19 - 20 μm	0.19 - 20 μm
Calibrated spectral range^a	0.248 - 2.1 μm	0.248 - 2.1 μm	0.248 - 2.1 μm	0.248 - 2.1 μm
Noise equivalent power^b	3 mW	3 mW	10 mW	10 mW
Rise time (nominal)^c	1.3 s	1.3 s	1.3 s	1.3 s
Calibration uncertainty^d	$\pm 2.5\%$	$\pm 2.5\%$	$\pm 2.5\%$	$\pm 2.5\%$
Repeatability	$\pm 0.5\%$	$\pm 0.5\%$	$\pm 0.5\%$	$\pm 0.5\%$
Energy mode				
Maximum measurable energy ^e	40 J	40 J	40 J	40 J
Noise equivalent energy ^b	0.2 J	0.2 J	0.2 J	0.2 J
Minimum repetition period	4.6 s	4.6 s	11.5 s	11.5 s
Maximum pulse width	123 ms	123 ms	390 ms	390 ms
Accuracy with energy calibration option	$\pm 5\%$	$\pm 5\%$	$\pm 5\%$	$\pm 5\%$
DAMAGE THRESHOLDS				
Maximum average power density				
1064 nm, 10 W, CW	45 kW/cm ²	45 kW/cm ²	45 kW/cm ²	45 kW/cm ²
10.6 μm , 10 W, CW	14 kW/cm ²	14 kW/cm ²	14 kW/cm ²	14 kW/cm ²
Maximum energy density				
1064 nm, 360 μs , 5 Hz	9 J/cm ²	9 J/cm ²	9 J/cm ²	9 J/cm ²
1064 nm, 7 ns, 10 Hz	1 J/cm ²	1 J/cm ²	1 J/cm ²	1 J/cm ²
532 nm, 7 ns, 10 Hz	0.6 J/cm ²	0.6 J/cm ²	0.6 J/cm ²	0.6 J/cm ²
266 nm, 7 ns, 10 Hz	0.3 J/cm ²	0.3 J/cm ²	0.3 J/cm ²	0.3 J/cm ²
PHYSICAL CHARACTERISTICS				
Effective aperture	25 mm \emptyset	25 mm \emptyset	25 mm \emptyset	25 mm \emptyset
Absorber (high damage threshold)	H9	H9	H12	H12
Dimensions	89H x 89W x 32D mm	89H x 89W x 106D mm	89H x 89W x 116D mm	89H x 89W x 40D mm
Weight (head only)	0.68 kg	0.99 kg	1.44 kg	0.87 kg
ORDERING INFORMATION				
Available output options	DB15, USB, RS-232 or Bluetooth	DB15, USB, RS-232 or Bluetooth	DB15, USB, RS-232 or Bluetooth	DB15, USB, RS-232 or Bluetooth
Compatible stand	STAND-S-443	STAND-S-443	STAND-S-443	STAND-S-443
Product page				

a. Calibrations at 2.1 to 2.5 μm and 10.6 μm are available on special request.
 b. Nominal value, actual value depends on electrical noise in the measurement system.
 c. With anticipation.
 d. Including linearity with power.
 e. For 360 μs pulses. Higher pulse energy possible for long pulses (ms), less for short pulses (ns).
 f. Minimum cooling flow 1.5 liters/min, water temperature $\leq 22^\circ\text{C}$, 1/8 NPT compression fittings for 1/4 inch semi-rigid tube. Contact Gentec-EO for clean deionized water cooling module option.